Care with radio

Connection to call systems





Call transmitter

- · Always with you: on the wristband, necklace or walker
- Red, easy to recognize button
- Easy to operate thanks to a large and smooth touch surface
- · Waterproof, with IP65 protection rating
- Nickel-free wrist strap
- · Necklace with strangulation protection
- Battery life of several years with CR2032 battery
- Monitoring of the battery status
- Weak batteries are indicated via radio and a clearly visible LED signal





Call receiver

- Call activation in nurse call systems, via potentialfree relay output
- Customerside assembly with call system-specific connection cable
- 32 call transmitters and 8 function transmitters can be programmed
- Acknowledge function reset calls via radio Care function - mute calls for 15 minutes Mute funktion - only evaluate priority calls
- Optionally with internal or external programming
- Display of operational readiness via clearly visible LED
- Detection and signaling of low battery voltage of the programmed transmitters
- Flexible power supply of 12-24 V AC or 12-32 V DC
- Small dimensions of only 35x80x20 mm





Wall transmitter

- Ideal for wireless call activation of care systems or for care at home
- RTS22 wall switch in Format 55, optionally with clearly visible red rocker
- Sensor wall switch RTS25, for call activation by a
- Acknowledgement wall switch for acknowledging calls, compatible with RCL07 and RCP25
- · Includes mounting plate and frame
- · Can be mounted using adhesive pads or screws
- Battery life of several years with CR2032 battery











RTS22 QUIT green





Care with radio

Mobile call for help





Socket pager

- Optical and acoustic signaling of personal calls
- Ideal for calls in the house, at the neighbour's or in the doctor's office
- Signaling continues until the call was acknowledged
- Up to 90 dB ringtone volume and optional flash LED
- 12 available melodies
- 32 call transmitters and 32 acknowledgement transmitters can be programmed
- Detection and signaling of low battery voltage of the programmed transmitters
- · No laying of cables, fits in any socket





APF03

Phone "FonAlarm"

- Automatically calls up to 5 previously saved phone numbers one after the other and plays a recorded voice message
- Easy alerting of neighbors, grandchildren or care services in emergency situations
- Up to 8 transmitters can be programmed for triggering a call
- Connection to a conventional, analogue telephone connection
- If the call for help is confirmed by the person being called, the integrated handsfree system can be used to speak
- Large buttons, high-contrast display, hearing aid compatible, extra loud ringtone with visual call indicator
- Night light function, 30 phone book entries, 5 speed dial keys, 10 quick dial keys
- Includes wristband transmitter RT26





MiniPager

- Receive calls from up to 64 Easywave transmitters on the move
- Optical, acoustic and haptic signaling with adjustable volume
- · Each transmitter has its own text on the display
- Each call must be acknowledged individually in order to stop signaling
- Easy configuration on a Windows PC
- Integrated battery with about. 48 hours runtime
- Charging time of only approx. 3 hours
- Clip for attaching to a belt
- Expandable charging cradle for up to 10 MiniPagers available



ACC-01



ACC-02





Phone: +49 3375 9037-0 Email: info@eldat.de